



RoHS

本产品符合我司QA-3-04-005
环境管理物质标准规范


包装图




Partial enlarged detail
局部放大图A
Scale比例 6:1



Step步骤1:



Step步骤2:



Step步骤3:

Applicable Product No. 适用产品料号	2625A-PXX09-H00
----------------------------------	-----------------

Poles Pin位	Pcs/Tray Pcs/盘	Tray/Carton 盘/箱	Pcs/Carton Pcs/箱
02	384	19	7296
03	312	19	5928
04	264	19	5016
06	192	19	3648

Packing step包装步骤:

Step 1: Place the inspected product, arrange neatly and in the same direction into the uptake plastic tray, the quantity cannot be reduced.

步骤1: 将检验好的良品,整齐并方向一致地摆放入吸塑盘,不可少数.

Specification of the uptake plastic tray: 2625SP-3850*3150*160

吸塑盘规格: 2625SP-3850*3150*160

Step 2: Overlap the plastic disks. When overlapping the plastic disks, place the upper and lower plastic disks in the same direction. Each 19 product disks and 1 empty plastic disk on the top layer are folded into 1 tie. Then wrap with PE film shaft shape.

步骤2: 将吸塑盘重叠,在重叠吸塑盘时,上下层吸塑盘方向需保持一致摆放,每19盘产品加最顶层放1PCS空吸塑盘叠起来为1扎,然后用PE膜井字型缠绕.

Step 3: Put 1 bundle of products bound with PE film in a carton, and put on a waterproof bag, then seal the carton with transparent tape, attach outer carton label.

步骤3: 一箱里放入PE膜捆好的1扎产品并套上防水袋,然后用透明胶带封箱,贴上下箱标签.

Note: when the carton is not full, filling material is required, cannot shake too much.

注: 不满箱时,需使用填充物,不可晃动太大.

Carton size: CB-400*330*260KK

纸箱规格: CB-400*330*260KK

Carton material: K=K; Carton thickness: 6~7mm

纸箱材质: K=K; 纸箱厚度: 6~7mm

一般公差

.X ±0.35

.XX ±0.25

.XXX ±0.15

X: ±2°

视角

视角

SMS 东莞市思索技术股份有限公司
Dongguan SESO Technology Co., Ltd.

图号: PK-2625A-PXX09-H00

名称: 2.50 WTB CONN. Packing

单位	比例	页次	版本	编号
mm	1:1	1/1	A0	A-000

20250619	A0	/	首次发行	程纳	张洪超
日期	版次	变更编号	变更内容说明	变更人	核准